

Communication Devices

AbleNet's AAC products are used by millions of people worldwide with a variety of medical and developmental conditions. From children with developmental language disorders, to individuals with severe physical disabilities that limit speech, AbleNet communication devices are available in a range of sizes and features.

When choosing a device, consider how many messages will be required, what access methods will be used, and whether the device is for a single person, or a group environment. For example, a strategically placed BIGmack® may be used by multiple users in a group home for reliably identifying shared needs. Meanwhile, a SuperTalker™ will grow with a child as his or her communication needs change over time.



Talking Brix™



BIGmack® & LITTLEmack®



BIG Step-by-Step™ & LITTLE Step-by-Step™



Step-by-Step™ with Levels



Lingo™ All-in-One-Kit



iTalk2™ & iTalk2™ with Levels



QuickTalker™ Communicators (7, 12, 23)



SuperTalker™ Progressive Communicator



FLASH™ Scanning Communicator



Jive!™ Handheld Communicator

MESSAGES : LEVELS	1 : 0	1 : 0	Unlimited Sequential : 0	Unlimited Sequential : 3	7 single, 1 sequential : 0	2 : 0 (2 : 3)	5	1, 2, 4, or 8 : 8	4 : Unlimited (12 overlays incl.)	Up to 100 equal cells per page / up to 10,000 pages
RECORDING TIME	10 sec.	2 minutes	2 minutes	4 minutes	7 @ 25 sec., 1 @ 60 sec.	2 minutes	6 min. / 12 min. / 20 min.	16 minutes	16 minutes	Up to 14 hours
SWITCH INPUT	No	1	1	1	No	2	No	8	4	1 USB
TOY / APPLIANCE OUTPUT / ECU	No	1	1	1	No	2	No	2	1	IR Capability
ACTIVATION AREA	1.8"	5 inches / 2.5 inches	5 inches / 2.5 inches	2.5 inches	0.6 inch	2.5 inches each	Static Locations: 2.167x1.20 in. / QT7: 3.38x2.65 / QT12: 2.17x1.68 / QT23: 1.20x1.20 in.	1.75 inches up to 7.75 inches	2 inches	3.5 inches x 2 inches
ACTIVATION PRESSURE	2 oz.	3-5 oz. / 2-3 oz.	3-5 oz. / 2-3 oz.	2-3 oz.	5-10 oz.	2-3 oz.	8 oz.	8 oz.	5-14 oz.	1 oz.
WEIGHT WITH BATTERY	1.5 Oz.	15.5 oz. / 8.5 oz.	15.5 oz. / 8.5 oz.	8.5 oz.	4.5 oz.	12.5 oz.	32 oz. (2 lbs.)	48 oz. (3 lbs.)	12 oz.	
BATTERY TYPE	Rechargeable	9-volt	9-volt	9-volt	Rechargeable Lithium Ion	9-volt	(4) AA Alkaline Batteries	4 AA	Rechargeable AA battery pack	Lithium-ion (8 hrs. of use)
ACCESSORIES AVAILABLE	No	Travel Strap, Mounting Plate, Additional switch top colors (business casual or semi-formal)	Travel Strap, Mounting Plate, Additional switch top colors (business casual or semi-formal)	Travel Strap, Mounting Plate, Additional switch top colors (business casual or semi-formal)	Includes: 2-4-8 keyguards, Belt Clip, Travel Strap, Wrist Mount	Travel Strap, Mounting Plate	No	Travel Strap, Mounting Plate, Adjustable Stand	Travel Strap, Mounting Plate, Colored Keyguards, Pillow Speaker, Memory Modules, Overlay Sleeves	Jacket including 2 white stylus / Carrying Case
SPECIAL FEATURES	Symbol Cover	Snap Switch Caps, 4 colors of Twist-off switch tops included	Snap Switch Caps, 4 colors of Twist-off switch tops included	Snap Switch Caps, 4 colors of Twist-off switch tops included	Ultra-portable, Head- phone Jack	Built-in Symbol Storage	Built-in symbols storage Flexible recording time by location	Built-in Overlay Storage and Step-by-Step functionality	Auto Overlay Detection, Overlay Storage, Step-by-Step functionality	Scrolling Cells / Character, Word, and Sentence prediction / IDV4Life Vocab library. Includes Picture Symbol Set